



Series RE-04

Multi-pin connection,
4 – 16 valve stations,
360 NI/min (0.366 Cv)

Design and function

Manifold system with integrated electrical connection including LED, manual override and built-in circuit protection. Double solenoid valves and 5/3-way valves require 2 stations on the manifold. The above order code covers only the manifold. The valves and the multi-pin plug with cable must be ordered separately.

The valve terminal is delivered pre-assembled and function-tested. If not specified with the order, valve configuration is as follows: Valves are mounted according to their order number, starting with high numbers on the side of the multi-pin, ending with low numbers on the opposite side, followed by blind plates (if ordered).