



Series RE-10

Multi-pin, AS-Interface
or fieldbus connection,
4 – 12 valve stations,
300 NI/min (0.305 Cv)

Design and function

Manifold system with integrated electrical connection including LED indicators. Each station can accommodate two 3/2-way valves or one 5/2- or 5/3-way valve. All connections are accessible from the front. The valves and the multi-pin plug with cable must be ordered separately. The manifold can be mounted with 4 M5 screws from bottom or from top using the mounting bracket RE-10-B-01 or on a DIN-rail (screws are included). The valve terminal is delivered pre-assembled and function-tested. If not specified with the order, valve configuration is as follows: Valves are mounted according to their order number, starting with high numbers on the side of the multi-pin, ending with low numbers on the opposite side, followed by blind plates (if ordered).